



B6106-6108, Nanfangmingzhu Commercial City, Longhua New District, Shenzhen 518109 China Tel: 0086-755 8996 1916 Mob: 0086-151 0755 0219 Fax: 0086-755 2857 0577 sales@wwlaser.hk www.wwlaser.com www.wwlaser.hk www.wisely-laser.com



















Washington, North Carolina 27889 (252) 975-1141

BAG-IN/BAG-OUT FILTER HOUSING

CAMFIL JOB#:

CAMFIL MODEL#

PREFILTER PART#

CHANGE-OUT BAG

FINAL FILTER PART#

CHANGE-OUT BAG


CAUTION: STOP AIRFLOW THROUGH HOUSING BY SHUTTING DOWN THE SYSTEM OR CLOSING **UPSTREAM AND DOWNSTREAM ISOLATION** DAMPERS BEFORE REMOVING DOOR, CONSULT YOUR SAFETY OFFICER AND READ INSTRUCTION MANUAL TO ENSURE PROPER FILTER INSTALLATION AND CHANGE-OUT.

Stainless Steel Nameplate-Black Marking





















B6106-6108, Nanfangmingzhu Commercial City, Longhua New District, Shenzhen 518109 China Tel: 0086-755 8996 1916 Mob: 0086-151 0755 0219 Fax: 0086-755 2857 0577 E-mail: wwlaser@gmail.com / sales@wwlaser.com Site: www.wwlaser.com / www.wisely-laser.com

Fiber Laser Marking Machine--MY-M10/20F-V

Features

There is a firm protection cover for the machine, it is very suitable for the machine sales in developed countries, it can protect you from hurt when the machine working.

Application Materials

WISELY laser marking machine can work with most metal marking applications, such as Stainless Steel, Brass, Aluminium, Steel, Iron etc, and can also mark on many non-metal materials, such as ABS, Nylon, PES, PVC, Makrolon.

Applicable Industries

Electronic Components: Resistors, Capacitors, Chips, Printed Circuit Boards, Computer Keyboard, etc.

Mechanical Parts: Bearings, Gears, Standard Parts, Motor,

Instrument: Panel Board, Nameplates, Precision equipment, etc. Hardware Tools: Knives, Tools, Measuring Tools, Cutting Tools, etc.

Automobile Parts: Pistons and Rings, Gears, Shafts, Bearings, Clutch, Lights, etc.

Daily Necessities: Handicrafts, Zipper, Key Holder, Sanitary Ware, etc.

Advantages

- 1) Protection Cover can protect the operater when processing.
- 2) High Precision: upto 0.0012mm, bring you the fantastic and satisfied marking effect.
- 3) Superior Laser Beam: the definition is 1 micron, 10 times as that of traditional products.
- 4) No Consumables: One Fiber marker can work for more than 10 years without any consumables.
- 5) Fast Speed: 800 standard characters per second, is 3 to 5 times above that of traditional products.
- 6) The fiber laser beam comes out from the IPG fiber device directly, no need to adjust the laser optical path.
- 7) With Motorized Up/Down Focus and scale plate, capable to make location precisely, it is convenient and swift.
- 8) Low consumption: <400W, is $1/25 \sim 1/10$ times as that of Diode and YAG, more economized and environmental.
- 8) Original Scaps controller, USB interface, swift and stable transmission, easy software operation, strong functions.
- 9) Original ScanLAB scan head, with good seal, capable to prevent dust and water, small volume, compact and solid.
- 10) Long lifespan of IPG laser module: 0.1-0.2 million hrs (light pumping YAG: several hundred hrs; semi-conductor: 10 000 hrs)
- 11) Strong Compatibility: TTF Font, SHX, BMP, DXF, AI, PLT and other format files output from CorelDraw, PS, AutoCAD, etc..
- 12) Integrated Air Cooling System: The cooling effect is more excellent than the water cooling effect in YAG laser, no maintenance.

 13) Deeper Marking: Max. 1.2mm stainless steel, suitable for the industries which needs high precision and depth marking effect.
- 3 1

Technical Parameters



Innovative Design for Sales
Protection Gover for Operator
Original Parts from Germany

Same quality, speed and preeision as other types

37534				
Туре	MY-M10F-V	MY-M20F-V		
Power	10W	20W		
Laser Wavelength	10	064nm		
Marking Area	150m	150mm*150mm		
Optional Marking Area	50mm*50mm / 100mm*100mm	/ 200mm*200mm / 300mm*300mm		
Marking Depth		≤1.2mm		
Marking Speed	800 standard	800 standard characters/second		

Minimum Line Width	0.012mm			
Minimum Character	0.15mm			
Repeated Precision	±0.003mm			
Fiber Laser Source	Imported with original packagingIPG in Germanywww.ipgphotonics.com			
Scan Head	Imported with original packagingScanLAB in Germanywww.scanlab.de			
Controller (SoftwareSAMlight)	Imported with original packagingScaps in Germanywww.scaps.com			
Life-span of Fiber Laser Module	100 000-200 000 hours			
Beam Quality	$M^2 < 1.5$			
Focus Spot Diameter	<0.01mm			
Output Power of Laser	10%~100% continuously to be adjusted			
Output Frequency of Laser	20KHz~100KHz continuously to be adjusted			
Power Stability (8h)	<±1%rms			
Marking Type	Dynamic Mark / Static Mark			
System Operation Environment	WindowsXP / Windows 732/64bits / Windows 832/64bits			
Cooling Mode Air coolingBuilt-in				
Temperature of Operation Environment 15°C~35°C				
Voltage	220V / 50HZ / single phase or 110V / 60HZ / single phase			
Power Requirement	<400W			
Computer Requested	There will be one PC with the machine			
Dimension (L*W*H)	600mm*750mm*1370mm			
Package Size	850mm*1000mm*1800mm			
Net Weight	150KG			
Gross Weight	200KG			
Optional (Not free of charge)	Rotary Device, Moving Table, other Automatic Matching System			

Shipment

We will effect shipment within 1-7 working days after receiving your payment.

Payment

By T/T, L/C, Collection and Payment on Delivery. Payment Terms can be negotiable.

Packaging

International Standard Packing--Plywood Case--free of fumigation. If the buyer needs the Certificate of Fumigation, we can help him, but the cost will be on the buyer's account.

Warranty

Whole machine has a warranty period of 12 months since the delivery.

This warranty does not cover items damaged while in the process of shipping. We do our best to package products in very safe shipping containers. If you purchase any component and pay for that shipping, then any item damaged in shipping must undergo a claim through your shipper. If you are person/company that paid for the shipping, then you must file that claim. We cannot send you another part for free while your claim is being processed. You may purchase a replacement part which we will attempt to mail to you again. If you are returning a part to be tested, then that part is considered "GOOD" until it is tested to be bad. You must insure the parts during shipment. If that part is damaged in shipping, then you must file a claim for shipping damage. Please understand that all shipping companies will conduct a damage investigation before they will pay restitution.

Training

Welcome to our company to learn how to operate the machine, we can offer you unlimited training free of charge.

Service

If you need local service, we can send our technician to your company within 3-7 days, but the buyer should pay the cost including the ticket, hotel and so on.

Samples


- 1) Samples available, we can make the samples at your request. If the package is small and you are planning to work with us, we can pay the TNT or FedEx freight.
- 2) All samples in the images are made by WISELY Fiber Laser Marker, copy right reserved!














Warning: Warranty for ScanLAB Scan Head









We use Germany IPG



There are about six types of "IPG" in China:

- (1) Original and brand-new from Germany, sold by IPG's distributor HM Laser in Beijing
- (2) Obsolete IPG, not current IPG
- (3) Second-hand
- (4) Reworked
- (5) Assembled, by so-called IPG technology or Germany technology
- (6) Copy

Which one will you get from other suppliers? You will get the ORIGINAL IPG from us I







TEST RESULTS
YTTERBIUM PULSED FIBER LASER
Model YLP-1-100-20-20-RG
S/N 1307016912

Form: 38169 Revision: 4 Page: 1 of 3

TEST RESULTS
YTTERBIUM PULSED FIBER LASER
Model YLP-1-100-20-20-RG
S/N 1307016912

Delay CH1 160.8 µs Form: 38169 Revision: 4 Page: 2 of 3

This product is covered by the U.S. Pat. Nos. 5,422,897 and 5,774,484 and any foreign counterparts thereof, and other patents pending.

The information and the following charts provided below is the result of tests performed in controlled environments by IPG Laser. These provided useful, but not warranted, information about the functions and performance of the product.

N	Characteristic	Symbol	Test Conditions	Min	Тур.	Max	Test Results	Unit
100	Optical characteristics		表示 克 先 当	PERSONAL PROPERTY.	PO MIL	9; BU B		0.000
1.	Mode of operation				pulsed		pulsed	
	Nominal average output	7000	RR = 20 kHz	19	20	21	20.1	W
2.	power	Pnom	RR = 200 kHz	19	20		20.4	W
3.	Output power adjusting range			10		100	tested	%
4.	Central emission wavelength	λ	P _{out} = P _{nom}	1055	1064	1070	1064.9	nm
5.	Emission bandwidth	Δλ	FWHM		5	10	4.2	nm
6.	Pulse duration	Δτ	FWHM P _{out} = P _{rom} RR = 20 kHz	90	100	120	107.5	ns
-	Laser switching ON time		0% → 90% Poom		170	250	161	μS
7.	Laser switching OFF time		100%→10%Pnom		170	250	209	μS
8.	Pulse repetition rate	RR	100/0 / 120/0	20		200	20 - 200	kHz
9.	Pulse energy	100	P _{out} = P _{nom} RR = 20 kHz		1		1.01	mJ
11.	Long-term average power instability		P _{out} = P _{nom} over 5 hrs			5	<3	%
12.	Red guide laser power		λ = 660 nm	0.3	0.5	1	0.5	mV
	Optical output (with buil	t-in optica	al isolator)	DESCRIPTION OF THE PARTY OF THE		A CONTRACTOR OF THE PARTY OF TH	STATE OF THE PARTY IS	
13.	Output beam diameter		86% level	6	7.5	9	6.8	mm
14.	Output beam divergence adjustment			minim	um of di	vergence	0.27	mra
	Electrical characteristics	海 & 海	THE RESERVE	200			B1	
15.					B1	7.5	24	V
16.	Laser module supply voltage			23	24	25	4.07	A
17.	Nominal current consumption		Pout = Prom		-	1	7.07	^
	General characteristics			1000	No. of Lot			
18.	Warm-up time to full				10		10	mir

200.00 (M/div 2000, 2001 - 2003 2000 / Cent - 2003

Fig. 1 Laser switching ON time (0% to 90% nominal output power)

Agilent Infinium Oscilloscope

Agilent Infinitum Oscilloscope






Fig. 4 Output spectrum at the RR = 20 kHz and nominal output powe



We use Germany Sean LAB







You will get the ORIGINAL SeanLAB from us I



SCANLAB CONTRACTOR

printed 21.Mai.2013

Tested Scan System: SCANcube 10
Article №: 111766
Serial №: 394016

Calibration: ± 11.70 degrees, mechanical

Statics Test Date: 16.Mai.2013							08:50:36	
X/Y Axis	Req. Optical Fu value	ill-Scale Angle tolerance	Required Opvalue	ptical Offset tolerance	Required S value	kew Angle tolerance	Passed	
Х	0.851 rad	± 5.0 mrad	0.000 rad	± 5.0 mrad	0.000 rad	± 1.5 mrad	Ø	
Y	0.851 rad	± 5.0 mrad	0.000 rad	± 5.0 mrad	0.000 rad	\pm 1.5 mrad	\square	

Dynamics		Test Date: 16.Mai.2013	08:52:04
Specification		-2-4-6-5-3-1-1-1-1-1-1-1-1-1-1-1-1-1-1-1-1-1-1	Passed
Oscillation Test	: 2		Ø
Oscillation Test	1		\square
Scan Field Test	Axis 2		\square
Scan Field Test	Axis 1		
Current Test Squ	uare Function		
Current Repetiti	ive Response		
Automatic Gain (Control		
Slew Rate Limit	Neg		☑
Slew Rate Limit	Pos		☑
Vector Matching			Ø
Vector Response			☑
Repetitive Match	ning		
Repetitive Respo	onse		

Wobble		Test Date: 16.Mai.2013	08:52:55
Scan Axis	Maximum Mechanical RMS		Passed
1	1.30 µrad		\square
2	1.30 µrad		V

Final Result PASSED

Final Test Rep	ort Page	1 of 1	Serial №: 394016
ORM 107			This report is generated with SCANLAB's automated Test System STS
Scan Axis 1, 2	A beam entering the entrance aperture first hits Scan Axis 1 and then Scan Axis 2.	Wobble RMS	The root mean square of a scanner's wobble for a specific time period
Calibration	Indicates the range of mechanical angles to which both scanners are edjusted. Calibration is performed at 95% of a scanner's full-scale setting	Optical Angle	axis 1 is kept un-deflected. If scan axis 1 is varied and scan axis 2 is kept un-deflected, the beam projects along the y-axis. Equals 2 times the mechanical angle
	TOTAL TO STREET WERE OF THE PROJECT OF THE TOTAL TOTAL TOTAL TO STREET THE STREET OF THE STREET THE	X/Y Axis:	A beam projects along the x-axis if scan axis 2 is varied and scan
Definition of Ter	ms		

Introduction of Sean Head made in China










vvvvv.jihekj.com Sean Head from Jinhaichuang Technology WWW.contury-sunny .com Sean Head from Belling Century Sunny Technology







The control card matters to the marking speed and precision! Each set of controller has password from Scaps.




You will get the ORIGINAL Scaps from usil











We can provide the Customized Automatic Matching System, just tell us your request by sales@wwlaser.hk