

Sampling

Mechanical samplers

- Easy handling
- Sturdy construction
- Easily decomposable
- Outlet opening in the handle
- Low weight
- Length: 1.5 m respectively 2 m
- Sample: about 600 g respectively 800 g

■ Application

Mechanical samplers are used for obtaining average samples. They allow the sampling up to a depth of 2 m.

■ Taking of a sample

Insert the closed sampler into the bulk goods. Open the chambers by a single turn of the handle and afterwards turn it back again. The specially shaped openings avoid a cutting of the grains. The original percentage of broken corns will not be increased. The sampler consists of two anodized aluminium tubes and can be cleaned easily by drawing them apart.

■ Technical data

length	1.5 m	2 m
diameter	40 mm	40 mm
openings	6	8
sample quantity	600 g	800 g
weight	1.8 kg	2.3 kg
Order-No.	1720 0500	1720 0510

We reserve the right to make technical modifications!

can be used in all possible storage places of cereals and pellets, like granaries, storage halls, trucks, railway waggons and similar

■ Pfeuffer GmbH
P. O. Box 248
D-97305 Kitzingen

■ Phone +49- 93 21- 93 69 -0
Telefax +49- 93 21- 93 69 -50
e-mail info@pfeuffer.com

